


ortofon

accuracy in sound



Technical specifications

2M models

2M Verso models

2M Premounted models



Model	2M Red	2M Blue	2M Bronze	2M Black	2M Black LVB 250	2M 78	2M Mono
Output voltage at 1 kHz, 5 cm/sec.	5.5 mV	5.5 mV	5 mV	5 mV	5 mV	4 mV	4 mV
Tracking ability at 315 Hz	70 μ m	80 μ m	80 μ m	80 μ m	80 μ m	70 μ m	70 μ m
Compliance, dynamic, lateral	18 μ m/mN	18 μ m/mN	20 μ m/mN	20 μ m/mN	22 μ m/mN	22 μ m/mN	22 μ m/mN
Stylus type	Elliptical	Nude Elliptical	Nude Fine Line	Nude Shibata	Nude Shibata	Spherical	Nude Spherical
Tracking force recommended	1.8 g (18 mN)	1.8 g (18 mN)	1.5 g (15 mN)	1.5 g (15 mN)	1.6 g (16 mN)	1.8 g (18 mN)	1.8 g (18 mN)
Load resistance	47 kOhm	47 kOhm	47 kOhm	47 kOhm	47 kOhm	47 kOhm	47 kOhm
Load capacitance	150 – 300 pF	150 – 300 pF	150 – 300 pF	150 – 300 pF	150 – 300 pF	150 – 300 pF	150 – 300 pF
Weight, Cartridge	7.2 g	7.2 g	7.2 g	7.2 g	7.2 g	7.2 g	7.2 g
Weight, Premounted	16.7 g	16.7 g	16.7 g	16.7 g	16.7 g	16.7 g	16.7 g

All specs at recommended tracking force

About the Ortofon 2M Series cartridges

Thank you for choosing the Ortofon 2M magnetic cartridge system for high performance sound reproduction of your favourite analogue records.

Our company has been working with sound reproduction since 1918. Ortofon developed its first phono cartridge in 1948, since then more than 300 different phono cartridges have been developed and manufactured. Reflecting our extensive experience in industrial design and technological know-how we have become the global leader in the manufacture and supply of phono cartridges.

The 2M Series has been engineered in accordance with the highest standards and is congruent with Ortofon's unrelenting commitment to providing the most precise and accurate reproduction possible without coloration.

The 2M Series comprises of three configurations: 2M for top mounting, 2M Verso for bottom mounting, and 2M Premounted for direct mount on s-shaped arms with universal mount. Each configuration consists of 2M 78, Mono, Red, Blue, Bronze, Black and Black LVB 250, which weight and size have been optimized to fit the most common turntables on the market to-day.

As a result of reviewer listening tests we feel confident that you will appreciate and enjoy the unique qualities of these cartridges.

ortofon




2M

Standard model for top mount headshells. We have optimized the design for ease of mounting the cartridge; the weight and dimensions fit the most common turntables on the market today.



2M Verso

For bottom mount headshells. 2M Verso allows for easy mounting on tonearms which do not allow the screws to pass through the top of the headshell.



2M Premounted

Designed for direct mount on s-shaped arms with universal mount. 2M Premounted provides correct Baerwald alignment with the majority of tonearms with universal mount.

Mounting the 2M cartridge

1. Remove stylus unit with stylus guard before working with leads and screws. Handle all parts carefully. (fig. 1-2)




Fig. 2

2. Note colours and channel indications on rear side of the body for correct connection of the tone arm leads. (fig. 3)




Fig. 3

3. The Ortofon packing contains a pair of screws with a thread length of 5 mm. The screws are to be used with headshell thicknesses of max. 3.5 mm. The 2M threaded mounting plate has a thickness of 3 mm.




Fig. 4

To check that you are using the right length of screws – please observe that screws must not touch the body under the mounting plate – look into the small openings on each side of the body. (fig. 4)




Fig. 5

Stylus care and maintenance

To obtain optimal sound reproduction, remove dust from stylus regularly by using the enclosed small brush.

If the headshell can be easily removed from the tone arm, we recommend that you turn the diamond upwards and brush gently forward in the direction of the diamond tip along the cantilever.

We do not recommend the use of propyl alcohol (or other cleaning fluids) for cleaning the cartridge, as the diamond cement as well as the suspension system could be seriously damaged and thereby ruin the cartridge.






Fig. 6




2M Premounted features

- Universal mount fitting matching S-shaped tonearms with standard H-4 bayonet mount.
- Provides correct Baerwald alignment with the major part of tonearms with universal mount.
- Gold-plated connectors for optimal audible connection.
- Distance to connector 52 mm.
- 2M Premounted cartridge weight: 16.7 g.



ortofon



Warning

This phono cartridge is only for mounting on tonearms and must not be used for other purposes.

2M



Scan and follow the QR code for setup
and support or find more information on
www.ortofon.com/support

ortofon
accuracy in sound

Ortofon A/S | Stavangervej 9 | DK-4900 Nakskov
Tel. +45 54 91 19 15 | www.ortofon.com